

**ENGLISH** 

#### **Datasheet**

# RS Pro 2.5A Radial Non-Resettable Wire Ended Fuse, 250 V

RS Stock No: 767-5058



#### **Product Details**

RS Pro radial non-resettable fuse withstands currents up to 2.5 A and voltages up to 250 V. It has thermoplastic body for added durability. This slow blow fuse forms a convenient and reliable solution to a vast array of application requirements.

#### **Features and Benefits**

- Slow blow fuse
- Base and cap in black thermoplastic
- Round pins in tin plated copper
- Vibration MIL-STD-202G
- Salt spray MIL-STD-202G
- Insulation resistance MIL-STD-202G
- Resistance to solder heat MIL-STD-202G
- Thermal shock MIL-STD-202G



## ENGLISH

### **Specifications:**

Body Height	7.7 mm
Body Length	8.35 mm
Body Material	Thermoplastic
Body Width	4.3 mm
Breaking Capacity (at Maximum Voltage Rating)	35 A at 250 V ac
Current Rating	2.5 A
Lead Orientation	Radial
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Voltage Rating	250 V
Voltage Rating	250 V
Wire Diameter	0.62 mm
Wire Length	22 mm
Wire Pitch	5.08 mm
Fuse Type	Time Lag
Nominal Resistance	0.0241 Ω
Standards Met	SEMKO, VDE, TUV, CSA, UL, CCC, KTL, PSE, RoHS