

Features

- 2 Gang
- Switched
- Double Pole
- Twin Earth
- Clip-On Cover Plate
- Matt Black Plate Finish
- Black Insert
- Decorative screwless plate

RS PRO Plug Sockets

RS Stock No.: 0845503



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Fits standard 35mm 2 gang back boxes
- Suitable for use with standard UK 13A plug tops

General Specifications

Dimensions (mm)	146 (W) x 86 (H) x 27 (D)
Insert Dimensions (mm)	142.5 (W) x 82.5 (H) x 2.5 (D)
Plate Dimensions (mm)	146 (W) x 86 (H) x 4 (D)
Plate Fixing Centres (mm)	120.6
Style	Screwless Complete
Finish	Matt Black
Insert Colour	Black
Anti Microbial Certified	No
Warranty (Years)	20

Mechanical Specifications

Termination Type	Screw
Terminal Size (mm)	Ø5
Terminal Torque Value (Nm)	2
Terminal Capacity - Solid (mm ²)	3 x 2.5 or 2 x 4
Twin Earth Terminals	Yes
Double Pole Switch	Yes
Minimum Back Box Depth (mm)	35
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40

Electrical Specifications

Frequency (Hz)	50
Resistive Load Rating (A)	13

Approvals

Standards Met	BS 1363-2
---------------	-----------