



D25033K

22mm 3 mode hammer

Selling Proposition

- Ideal for drilling anchor and fixing holes into concrete and masonry from 4 to 22 mm in diameter
- Rotation-stop for light chiselling applications in brick, soft masonry and occasionally concrete
- Impact-stop for drilling in wood, steel, ceramic and screwdriving applications
- Large hammer mechanism delivers high performance with low stress to the critical components resulting in better durability
- Mechanical clutch eliminates sudden high-torque reaction should the bit jam
- Electronic variable speed for total control in any application

Standard Equipment

- Multi position side handle
- Depth stop
- Heavy duty carrying case

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Tool Holder	SDS-Plus
Power Input	710 Watts
Battery chemistry	
Voltage	
Battery Capacity	
Power Output	590 Watt
Impact energy (EPTA 05/2009)	2.0 J
No Load Speed	0-1550 rpm