



Product data sheet

Power tools for trade & industry

Metal Cut-off Saw

PRO GCD 18V-355



World's first cordless 18V dry cutter with 355 mm sawblade

The most important data

Battery voltage	18.0 V
Weight excl. battery	19.8 kg

Part Number 0 601 B59 000

Technical data

Technical data

No-load speed	1,430 1/min
Weight excl. battery	19.8 kg
Battery voltage	18.0 V
Packaging dimensions (width x length x height)	482 x 683 x 498 mm
BITURBO	No

Noise/vibration information

Sawing metal

Vibration emission value ah	3.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- 18V brushless motor delivers cordless power equal to a 2000W corded dry cutter
- Dry cutter allows fast, cold, and spark-reduced cuts without deburring at constant cutting depth
- Thanks to the precise laser cutting line, it is easy to position the workpiece and align the cut
- Perfect keyless workpiece clamping with keyless adjustable fence
- Overload indicator to prolong lifetime of battery and sawblade



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

