

FEATURES

- Density of 1.5 g/cm³
- Length of 1 m
- Width of 600 mm
- Thickness of 10 mm
- Stretches up to twice its original length
- Suitable for use with water, acids, alkalis and fuels
- Black in colour
- Minimum operating temperature of -20 °C
- Maximum operating temperature of +70 °C

RS PRO Black Rubber Sheet, 1m x 600mm x 10mm

RS Stock No.: 506-3028



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Natural Rubber Sheets



Product Description

This black natural rubber sheet is ideally suited to provide a protective barrier against corrosive substance or insulation from noise in industrial and factory settings. The commercial-grade rubber sheet can stretch up to twice its original length before breaking and offers good resistance to acids and alkalis.

General Specifications

Colour	Black
Suitability	Cold Water, Dilute Acid, Dilute Alkali, Ethylene Glycol, Fuel, Hot Water, Oil
Finish	Smooth
Material	Natural
Application	Indoor use

Mechanical Specifications

Length	1000mm
Thickness	10mm
Width	600mm
Density	1.5g/cm³
Elongation	200%
Hardness	70+/-7 Shore
Tensile Strength	4 N/mm ²
Specific Gravity	1.46g/cm ³

Operation Environment Specifications

Maximum Operating Temperature	+70°C
Minimum Operating Temperature	-20°C

Natural Rubber Sheets



Approvals

Compliance/Certifications	RoHS