

2005 0701

Tool trolley

Code 2003554 ETIM EC011808
 EAN 4010886877784 UNSPSC 56-12-18-02
 Country of origin Germany eCl@ss 21-07-11-00
 Customs tariff number 94032080



Article description

- Body:
 - Dimensions: H 812 x W 771 x D 478 mm
 - Working platform in ABS, with compartments for small parts
 - Manoeuvrable and easy to steer with drive/steer handle
 - Side walls with Euro perforation 10 x 38 mm for attaching hooks and tools
 - Heel and impact protection for your safety
 - Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
- Drawers:
 - Central locking with cylinder lock
 - Wide drawers (W 640 x D 400 mm) fully extendable, removable
 - Safety locking per drawer, one-hand operation
 - Guide rails with ball bearings
 - Can be individually equipped with lengthwise and crosswise dividers (can be ordered individually)
 - Load capacity per drawer 40 kg, bottom heavy-duty drawer 60 kg
 - Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
 - GEDORE High-performance chassis:
 - Total load capacity 1000 kg static (750 kg dynamic)
 - 2 GEDORE heavy-duty wheels with roller bearings (fixed castors, 200 mm)
 - 2 GEDORE easy-running wheels with ball bearings (swivel castors, 125 mm), both with total brake each
 - The GEDORE trapezoidal axle construction secures smooth running, manoeuvrability and track-keeping also in case of maximum loads
- Accessories:
 - Length- (LT) and crosswise (QT) dividers from zinc-plated sheet steel (can be ordered individually)
 - Can be equipped with GEDORE tool modules (1500 ES/1500 CT or 2005 CT)
 - Optionally extendable with GEDORE tool chests, rear panels and tool holders
 - Further drawer versions upon request
 - Special colours and designs on request
 - Delivery without tools and accessories

Article information

| | | | |
|-------------------------------|-----------------------|---|---|
| Contents (Qty of pieces) | 1 | Number of drawers | 8 |
| Net weight [kg] | 87 kg | Load capacity per drawer [kg] | 40 kg |
| Total width [mm] | 865 mm | Drawer type | 7x Type 1, H = 67 mm 1x Type 3, H = 207 mm |
| Total height [mm] | 1.020 mm | Fixed roller diameter (2x) | 200 |
| Surface | powder-coated | Swivel castor diameter with brakes (2x) | 125 |
| Total depth [mm] | 605 mm | Single pull-out stop | no |
| Material | sheet steel | Number of wheels | 4 |
| Colour | GEDORE blue, RAL 5017 | Working height | 985 |
| Dimension (L x W x H) | 1.020 mm x 865 mm x | Static load carrying capacity [kg] | 1000 kg |
| Load capacity kg | 750 kg | Load capacity heavy duty drawer [kg] | 60 kg |
| Number of crosswise dividers | 2 | RAL colour tone | blue |
| Number of lengthwise dividers | 3 | | |