

Previously known as: PuretoughP1100



Multi Purpose



Light Duty

Abrasion-resistant light-duty gloves, combining superb comfort and mechanical protection

- **Improved durability:** HyFlex® 11-421 multipurpose gloves feature durable polyurethane coating, helping them attain ANSI level 4/EN level 3 abrasion resistance levels
- **Increased environmental friendliness:** Their PU coating is manufactured using a water-based process that is kinder to the environment
- **Reduced surface defect risks:** These HyFlex® gloves' silicone-free design also limits the risk of contaminant transfer to metal prior to painting
- **Minimized health risks:** Their formulation is 100% DMF-free, keeping wearers out of harm's way
- **Elevated comfort:** Fine, stretchable stitches significantly augment comfort levels
- **Easy identification:** HyFlex® 11-421 light-duty gloves' color-coded green indicator button reveals light, ANSI A1/EN ISO A cut resistance



Industries

- Automotive
- Machinery and Equipment

Applications

- Picking, fastening components
- Final assembly

Previously known as: PuretoughP1100

Key Features

- **Water-based polyurethane coating:** Durable, yet more eco-friendly
- **DMF- and silicone-free:** Fewer hazards, suitable for spray-painting
- **Fine, stretchable stitches:** For truly comfortable safety gloves

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-421	Finishing: Palm Coated Coating Material: Water-Based polyurethane Liner Material: Nylon Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	235-260 mm 9.25-10.23 inches	Black	• 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.