

SAKQ 4/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Cross-connector (terminal), when screwed in, grey, Number of poles: 10, Pitch in mm (P): 6.10, Insu- lated: No, Width: 6 mm
Order No.	1129340000
Type	SAKQ 4/10
GTIN (EAN)	4032248996186
Qty.	20 items
Local product	Only available in certain countries

SAKQ 4/10

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

General ordering data

Local product	Only available in certain countries
---------------	-------------------------------------

Dimensions and weights

Depth	15 mm	Depth (inches)	0.5906 inch
Height	60.6 mm	Height (inches)	2.3858 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	17.25 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Colour	grey
--------	------

System specifications

PE connection	No
---------------	----

Additional technical data

Type of fixing	when screwed in	Explosion-tested version	No
----------------	-----------------	--------------------------	----

Dimensions

Pitch in mm (P)	6.10 mm
-----------------	---------

General

Number of poles	10
-----------------	----

Rating data

Rated voltage	400 V
---------------	-------

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		