

# 18V Impact Driver LXT

## DTD156Z

DTD156 is a cost-effective cordless impact driver powered by 18V LXT Li-Ion battery.



### TECHNICAL SPECIFICATIONS

Voltage	18 v
Standard Bolt	M5-M14
High Tensile Bolt	M5-M12
Coarse thread (length)	22 - 125 mm
Max Fastening Torque	155 Nm
No Load Speed	0 - 2500 rpm
Battery Type	Lithium-ion
Vibration: Fastening Bolt	10.0 m/sec <sup>2</sup>
Vibration K factor	1.5 m/sec <sup>2</sup>
Noise sound pressure	92 dB(A)
Noise sound power	103 dB(A)
Noise K factor	3 dB(A)
Body only machine	✓
Net weight	1.3 - 1.6 kg
Driving Shank	6.35mm (1/4") Hex
Machine Screw	M4-M8
Impacts per Minute	0 - 3,000 ipm

### USER BENEFITS

- Electric brake
- Variable speed control by trigger
- Forward / reverse rotation
- LED job light
- Ergonomically designed high comfort grip.

[Link to product - makitauk.com](https://www.makita.com)



# RELATED PRODUCTS

(Recon

■ OTHER