

74 06 200 T

High Leverage Diagonal Cutter with tether attachment point



- With integrated forged axle for heaviest duty
- Suitable for all types of wire including piano wire
- High cutting performance with minimum effort due to optimum co-ordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
- Pliers with integrated, insulated tether attachment point for a tool tether

20 % less effort required

compared to conventional diagonal cutters of the same length.

With integrated forged joint axle.

Article No.	74 06 200 T
EAN	4003773081845
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Head	
Style	0
Insulation standard	IEC 60900 DIN EN 60900
Cutting capacities medium hard wire (diameter) Ø mm	4,2
Cutting capacities hard wire (diameter) Ø mm	3,0
Cutting capacities piano wire (diameter) Ø mm	2,5
Nominal size	200 mm
Length mm	200
Net weight g	311

technical change and errors excepted