

# Bosch GLM 40 Professional Laser Measure



**BOSCH**  
Invented for life

## All relevant functions in a compact design

- Distance measurement, area calculation, volume calculation – all intuitive to use
- Illuminated, three-line display maximises readability
- Memory function enables easy access to the last ten measurements
- Robust, shockproof housing with IP54 protection class (splash and dust protection)
- Reliable measuring results in all circumstances, proven by ISO certification



## Technical Data

Laser diode	635 nm, < 1 mW
Measurement range	0.15mm – 40m
Laser class	2
Measurement accuracy, typical	+/- 1.5 mm
Measurement time, typical	< 0.5 s
Measurement time, max.	4 s
Power supply	2 x 1.5 V LR03 (AAA)
Automatic deactivation	5 min.
Weight, approx.	0,09 kg
Units of measurement	m/cm, ft/inch
Memory capacity (values)	10
Battery lifetime, individual measurements, approx.	5.000
Dust and splash protection	IP 54

