

Features

- UL approved Nylon 66, 94V-0
- Color: White
- (standard), black color available.
- Feature: Low Smoke and Halogen Free cable tie suitable for various industry, also household DIY and gardening.
- Application: One piece self-lock cable tie save the time and make effective for installation.
- Easy to thread.

RS PRO Cable Ties

RS Stock No.: 389870



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These cable ties are made from Nylon 66(also known as nylon 6.6), UL 94V0 flame rated. The ties are suitable for binding components or cable and have a non-release ratchet lock action. Ideal for cable and wire management.

General Specifications

Type	Non-Releasable
Colour	White
Material	Nylon 66
UV Resistant	No
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	85°C
Fire Behaviour	Self-Extinguishing
Quantity	250

Mechanical Specifications

Length	190mm /7-1/2"
Width	4.8mm / 0.19"
Min. Loop Tensile Strength(lbs/kgf/N)	50lbs / 22kgf / 222N
Maximum Bundle Dia.	49mm

Approvals

Standards Met	RoHS , SVHC , HF
---------------	------------------

