

## 4 17X19

### Double ended ring spanner

straight

Code	ETIM
6054760	EC002188
EAN	UNSPSC
4010886605479	27-11-17-05
Country of origin	eCl@ss
Germany	21-04-01-06
Customs tariff number	
82041100	



### Article description

- Acc. to DIN 837 Form B, ISO 3318, ISO 1085
- Flat pattern
- Thin walled rings
- UD-profile
- Vanadium steel 31CrV3, chrome-plated
- \* not standardised

### Article information

Contents (Qty of pieces)	1	Standard	ISO 3318 ISO 1085
Version/Execution	<b>straight form, flat design, with thin-walled rings</b>	Width across flats 1 [mm]	17
Net weight [kg]	0,098 kg	Width of head 2 [mm]	28 mm
Total length [mm]	185 mm	Head height 1 [mm]	8,5 mm
Total width [mm]	27 mm	Width of head 1 [mm]	25,5 mm
Total height [mm]	9 mm	Width across flats [mm]	17x19
Surface	chrome-plated	Width across flats 2 [mm]	19
Material	31CrV3	Ring profile	UNIT-DRIVE