

Data sheet for Active Interface Modules Booksize

Article No. : 6SL3100-0BE31-2AB0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Electrical data

Number of phases	3 AC
Line voltage	380 ... 480 V

Connections

Line side	
Design	M8 bolt
Conductor cross-section	2.5 ... 120 mm ² (AWG 14 ... AWG -3)
PE conductor	M8 Screw

Mechanical data

Degree of protection	IP20 / UL open type
Type of construction	Booksize
Net weight	36.6 kg (80.69 lb)
Dimensions	
Width	300 mm (11.81 in)
Height	380 mm (14.96 in)
Depth	270 mm (10.63 in)

Standards

Compliance with standards	cURus
---------------------------	-------

Rated data

Input current	192 A
Current requirement at 24 V DC, maximum	1.20 A

General technical specifications

Sound pressure level	68 dB
Losses	0.585 kW

Ambient conditions

Cooling air throughput	0.167 m ³ /s (5.900 ft ³ /s)
Type of cooling	Internal air cooling