

FEATURES

- Cable protection
- Slotted construction
- Significantly lower fire risk, due to selfextinguishing nature
- Slot gaps are 8mm

RS PRO Grey Slotted Panel Trunking - Open Slot, W25 mm x D30mm, L2m, PVC

RS Stock No.: 758-9279



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Brought to you by RS Pro, this open slot PVC cable trunking is versatile and cost effective. Used in any application where cable protection is essential, this cable trunking has flexible slots to allow easy slide-on and slide-off of the cable cover. The open slot construction also allows for cables to be threaded into and out of the trunking at any point. The trunking is made from high impact, warp proof PVC, and is self-extinguishing to UL94-V2. This means the trunking is suitable for commercial applications, with an emphasis on safety and long-life. Whether you are running cable from switchboards for IT applications, or power and network leads for a busy office or factory floor, this cable trunking is ideal. All models are highly reliable and excellent quality.

General Specifications

Trunking/Chain Type	Slotted Panel Trunking		
Material	PVC		
Colour	Grey		
Fire Behaviour	Self-extinguishing		
Applications	Offices and indoor work spaces, at various lengths, Electrical workshops, Schools, Hospitals, Hotels and anywhere with customers walking amongst cables		

Mechanical Specifications

Length	2m
Width	25mm
Depth	30mm
Slot Type	Open
Slot Gap	8mm

Operation Environment Specifications

Operating Temperature Range	Upto 50°C
Maximum Service Temperature	85°C




Approvals


Standards Met	CE, CSA, RoHS Compliant, UL 94 V-0, UL 94 V-2, UL
	F97527

RS Stock Number	W (mm)	H (mm)	B (mm)
758-9204	25	30	6
758-9213	25	40	9
758-9216	25	60	13
758-9210	25	80	18
758-9229	40	40	11
758-9222	40	60	13
758-9226	40	80	10
758-9235	60	40	9
758-9238	60	60	13
758-9232	60	80	10
758-9241	60	100	15
758-9244	80	60	13
758-9248	80	80	13
758-9257	80	100	15
758-9250	100	40	11
758-9254	100	80	14
758-9263	100	100	16
758-9266	120	60	17

RS Stock Number	W (mm)	H (mm)	B (mm)
758-9260	15	25	6
758-9279	25	30	6
758-9272	25	40	10
758-9276	25	60	13
758-9285	25	80	19
758-9288	40	40	10
758-9282	40	60	13
758-9291	40	80	11
758-9294	60	40	10
758-9298	60	60	13
758-9308	60	80	11
758-9301	60	100	15
758-9305	80	60	13
758-9314	80	80	13
758-9317	80	100	15
758-9311	100	40	11
758-9320	100	80	13

NARROW 4mm SLOT





STANDARD 8mm SLOT

