



3315Z0

The 3315Z0 LED light: the lightweight compact design houses 3AA batteries that power a single LED for 138 lumens of super bright LED light. Safety approved for the most volatile work environments ATEX Zone 20, the 3315Z0 LED light is one of the most efficient torches on the market today. The 3315Z0 LED light: Compact light, huge LED performance.



DIMENSIONS

Length	6.14" (15.6 cm)
---------------	-----------------

MATERIALS

Body	Anti-static Impact Modified PC/PBT
O-Ring	EPDM
Lens	Anti-static coated Polycarbonate (PC)

COLOURS

 High Visibility Yellow
--

LIGHT SPECS

Lamp Type	LED
------------------	-----

POWER

Battery Size	AA
Battery Type	Alkaline
Battery Quantity	3
Batteries Included	yes
Volts	4.5v

WEIGHT

Weight With Batteries	6.2 oz (176 gr)
Weight Without Batteries	3.7 oz (105 gr)

SWITCH

Switch Type	Push Button
Light Modes	On / Off

CERTIFICATIONS

ATEX Zone 0

OTHER

Minimum Pack	1
--------------	---

FL1 STANDARD	HIGH
	138 LUMENS
	19h 0mins
	146m
	5350cd
	IP67

ACCESSORIES



0770
Helmet Light Holder



0782
Helmet Light Holder