



Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP unmanaged switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP
Port Ethernet	10BASE-T/100BASE-TX - 5 port(s) copper cable
Maximum number of switches in cascade	Unlimited

Complementary

Integrated connection type	1 M12 port copper cable
Transmission support medium	Twisted shielded pairs cable CAT 5E for copper cable
Ethernet service	Automatic negotiation of 10/100 Mbit/s and duplex mode Auto MDI/MDX Storage and re-routing of received data
[Us] rated supply voltage	24 V
Supply voltage limits	18...32 V DC SELV
Power consumption in W	3.2 W
Electrical connection	Removable M12 connector 5 ways power supply
Mounting support	35 mm symmetrical DIN rail
Marking	CE
Local signalling	1 LED power supply 1 LED per channel copper port activity
Ethernet cabling system	TF switches
Width	60 mm
Height	126 mm
Depth	31 mm
Product weight	0.21 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ambient air temperature for operation	0...60 °C
IP degree of protection	IP67
Standards	CSA C22.2 No 142 CUL 508

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0622 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available End of Life Information
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------