



## **Datasheet**

## RS Pro 3301 Series 2.5mm Pitch Straight PCB Terminal Block with Push In Termination, PCB Mount, 3 Way

RS Stock No: **874-5433** 



## **Specifications:**

Body Orientation	Straight
Colour	Grey
Current Rating	2 A
Depth	13 mm
Gender	Female
Length	9 mm
Material	Nylon 66
Mounting Type	PCB
Number of Contacts	3
Number of Rows	1
Pitch	2.5 mm
Termination Method	Push In
Type	PCB Terminal Block
Voltage Rating	300 V
Width	12 mm

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



## ENGLISH

American Wire Gauge	20 to 22 AWG
Insulation Withstands Voltage	2500 V ac
Operating Temperature Range	-40 to +105°C
Insulation Resistance	500 mΩ