

Datasheet

5.5 MM NUT SPINNER SCREWDRIVER

RS Stock number 460-1691



Material:

Chrome vanadium steel (50bv30) for blades, extrusion acetate handle

Finish:

Satin chrome finish, lacquer coating inner hole and red handle

Hardness:

Heat treated to HRC 48 – 51 degree for nut spinner driver blades

Contents:

1 pc - 5.5 mm nut spinner screwdriver with red colour handles
(length of blade : 125mm, overall length -- 226mm, remove the magnet from the steel blade, dia. 7.2mm)

Remark:

Torque, dimensions and gauge tests meet din-3125 standard