

# RLS4MPZ

4 pole loudspeaker receptacle, D-Size front mounted, 3/16" flat tabs contacts



## Article Variations

Article Name	Details	Packaging
RLS4MPZ	3/16" flat tabs contacts	BULK

## Technical Information

### Product

<b>Title</b>	RLS4MPZ
<b>Connection Type</b>	Loudspeaker Connectors

### Electrical

<b>Rated current</b>	continuous 30 A rms
<b>Contact resistance</b>	≤ 5 mΩ
<b>Insulation resistance</b>	> 1 GΩ
<b>Dielectric strength</b>	4 kV dc
<b>Rated Voltage</b>	250 V

### Mechanical

<b>Lifetime</b>	> 1000 mating cycles
<b>Chassis shape</b>	D
<b>Wiring</b>	flat tab ( 4.8 × 0.5 mm ) or soldering
<b>Mounting direction</b>	Front mounting or rear mounting

### Material

<b>Contact</b>	Bronze
<b>Contact plating</b>	Ag
<b>Shell</b>	PA6+30%GF

### Environmental

<b>Temperature range</b>	-30 °C to +80 °C
<b>Flammability</b>	UL94 V-0
<b>Solderability</b>	complies with IEC68-2-20