



Cut



Medium Duty

Cut and abrasion-resistant gloves granting excellent dexterity for medium-duty tasks

- **Advanced durability:** Thanks to their nitrile foam-coated palm, EDGE™ 48-706 nitrile gloves offer a good grip and protection against cuts and abrasion in dry and slightly oily environments, making them ideal substitutes for heavy-duty leather and PU palm dipped, cut-resistant knitted gloves
- **Increased protection:** EDGE™ 48-706 safety gloves feature EN ISO 13997 level C and ANSI level A3 cut resistance, and meet EN 420 (general requirements) and EN 388 (mechanical hazards) safety standards
- **Enhanced comfort:** These breathable work gloves possess a seamless liner that elevates comfort without sacrificing dexterity, while delivering great value at an affordable cost
- **Food handling compliance:** Made of FDA-compliant materials, these protective gloves are safe for food handling and packaging



Industries

- Automotive
- Construction
- Glass manufacturing

Applications

- General maintenance
- Hardware assembly
- Machining / Stamping / Cutting
- Molding
- Plastic injections
- Raw material handling
- Seat and frame build

Key Features

- ◊ **Nitrile foam coating:** Good grip in dry or slightly oily conditions
- ◊ **Enhanced cut protection:** Safer handling of sharp edges or materials
- ◊ **Breathable and seamless liner:** For comfortable and tactile work gloves

Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



EN388: 2016



4X43C

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE™ 48-706	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: HPPE, Fiber glass, Nylon, Polyester, Spandex Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	220-270 mm / 8.66-10.63 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.