








RECOMMEND MINIMUM MOUNTING PITCH

2.5-3.8mm RECOMMEND
PANEL THICKNESS



PANEL CUT OUT



PCB LAYOUT
(CONNECTOR TOP VIEW)

- RJ45 CONTACTS
- RJ45 SHELL GROUND CONTACT
- SHIELD BOX LEGS
- CONNECTOR LOCATION PINS

RJXS8FP15HP

- SERIES PREFIX
- CONTACT LAYOUT (RJ45 STYLE)
- GENDER
- THERMOPLASTIC 2.5mm to 3.8mm WITH CAP
- TRANSMISSION CLASS (CAT5e)
- HORIZONTAL MOUNT (PCB THRU HOLE)
- POTTED



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE:		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER		Amphenol		Amphenol Australia Pty.Ltd, 22 Industry Blvd Carrum Downs, VIC 3201	
LINEAR	ANGULAR	MATERIAL:	DRN: J.W	DATE: 24/08/2023	TITLE:		PART No:
X.X ±10	X" ±1	SEE COMPONENTS	CKD: P.M.	DATE: 24/08/2023	XLRnet, HORZ, IP65, POTTED, UNSHIELDED, W/CAP,PANEL		RJXS8FP15HP
X.X ±5	X" ±30'	DO NOT SCALE	APP'D: P.M.	DATE: 24/08/2023	DRAWING No.		REV
X.XX ±1	X"XX" ±15'	FINISH: SEE COMPONENTS	SCALE: NTS	SIZE: A3	THICKNESS 2.5-3.8		1
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS		THIRD ANGLE PROJECTION		SHEET		2/2	
DIMENSIONS IN MILLIMETRES							