


Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at http://www.download.phoenixcontact.com. The General Terms and Conditions of Use apply to Internet downloads.

▶ Extract from the online catalog



Header, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, mounting: Soldering

The illustration shows a 15-position version

Order No. 1759075

Ord designation MSTB 2,5/ 8-G-5,08

EAN 4017918030544

Pack 50 Pcs.
Customs tariff 85369010

Catalog page information Page 166 (CC-2005)

▶ Technical data

Dimensions / positions

Pitch 5.08 mm Dimension a 35.56 mm

Number of positions 8

Pin dimensions 1 x 1 mm Hole diameter 1.4 mm



Technical data

| Insulating material group | Illa |
|------------------------------------|--------|
| Rated surge voltage (III/3) | 4 kV |
| Rated surge voltage (III/2) | 4 kV |
| Rated surge voltage (II/2) | 4 kV |
| Rated voltage (III/2) | 320 V |
| Rated voltage (II/2) | 400 V |
| Connection in acc. with standard | EN-VDE |
| Nominal current I _N | 12 A |
| Nominal voltage U _N | 250 V |
| Maximum load current | 12 A |
| Insulating material | PBT |
| Inflammability class acc. to UL 94 | V0 |
| | |




▶ Certificates


| Certificate logos | Ce | rtif | icate | loa | os |
|-------------------|----|------|-------|-----|----|
|-------------------|----|------|-------|-----|----|

| ⑤P ₹1 | | |
|--------------------------------|-------|--|
| UL | | |
| Nominal voltage U _N | 300 V | |
| Nominal current I _N | 10 A | |
| CSA | | |
| Nominal voltage U _N | 300 V | |
| Nominal current I _N | 10 A | |



▶ Drawings







▶ Accessories

| Item | Designation | Description |
|-------------|--------------------------|---|
| Assembly | | |
| 1759981 | MSTB-BF | Mounting flange, for fixing both ends of the header onto the PCB, green insulating material, with M 2 x 14 screws and nuts. |
| 1755477 | MSTB-BL | Keying cap, for forming sections, plugs onto header pin, green insulating material |
| Marking | | |
| 1051993 | B-STIFT | Marker pen, for manual labeling of unprinted Zack strips, smear- proof and waterproof, line thickness 0.5 mm |
| 0804293 | SK 5,08/3,8:FORTL.ZAHLEN | Marker card, printed horizontally, self-adhesive, 12 identical decades marked 1-10, 11-20 etc. up to 91-(99)100, sufficient for 120 terminal blocks |
| 0805085 | SK 5,08/3,8:SO | Marker card, self-adhesive, marking according to customer requirements |
| 0805412 | SK 5,08/3,8:UNBEDRUCKT | Marker cards, unprinted, with pitch divisions, self-adhesive, 10-section marker strips, 12 strips per card, can be labeled with M-PEN |
| Plug/Adapte | er | |
| 1734401 | CR-MSTB | Coding element, inserted into the recess in the header or the inverted plug, red insulating material |



▶ Additional products

Item Designation Description



| General | | |
|---------|---------------------------|--|
| 1872758 | A-ICV 2,5/ 8-G-5,08 | Header, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, mounting: Mounting rail |
| 1873113 | FKC 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Spring-cage connection |
| 1902178 | FKCT 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Spring-cage connection |
| 1874015 | FKCVR 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Spring-cage connection |
| 1873715 | FKCVW 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Spring-cage connection |
| 1777345 | FRONT-MSTB 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 320 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |
| 1786462 | IC 2,5/ 8-G-5,08 | Header, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, mounting: Soldering |
| 1786006 | ICV 2,5/ 8-G-5,08 | Header, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, mounting: Soldering |
| 1757077 | MSTB 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |
| 1764235 | MSTB 2,5/ 8-STZ-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |
| 1808874 | MSTBC 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 320 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Crimp connection |
| 1809569 | MSTBC 2,5/ 8-STZ-5,08 | Plug component, nominal current: 12 A, rated voltage: 320 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Crimp connection |
| 1769078 | MSTBP 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |
| 1781043 | MSTBT 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |
| 1824418 | MSTBU 2,5/ 8-ST-5,08-FL | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |
| 1824188 | MSTBU 2,5/ 8-STD-5,08 | Plug component, nominal current: 12 A, rated voltage: 320 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |
| 1831375 | MSTBVK 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 320 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |
| 1792304 | MVSTBR 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |

MSTB 2,5/ 8-G-5,08



| | | CONTACT |
|---------|------------------------|--|
| 1792812 | MVSTBW 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |
| 1917969 | QC 0,75/ 8-ST-5,08 | Plug components, 5.08 mm pitch, color: green, no. of positions 8, dimension a 35.56 mm |
| 1883310 | QC 1/ 8-ST-5,08 | Plug component, nominal current: 10 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Insulation displacement connection QUICKON |
| 1826348 | SMSTB 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |
| 1853078 | TMSTBP 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 250 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |
| 1833878 | UMSTBVK 2,5/ 8-ST-5,08 | Plug component, nominal current: 12 A, rated voltage: 320 V, pitch: 5.08 mm, no. of positions: 8, type of connection: Screw connection |



▶ Address

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Phone +49 5235 3 00
Fax +49 5235 3 1200
http://www.phoenixcontact.com
Phoenix Contact

Technical modifications reserved;