

FEATURES

- Manual drain
- 40 micron filtration
- Integral square gauge
- · With bracket

RS PRO

Filter / Regulator & Lubricator

RS Stock No.: 2395723



Manual Drain, Integral Square Gauge
With bracket

Product Description

Part No.	Body Size	Port Size	Flow Rate
2395723	2000	G1/4"	1200 l/min



Features

- Manual drain
- 40 micron filtration
- Integral square gauge
- With bracket

General Specifications

Maximum working pressure	10 bar
Working temperature	-5°C to +60°C (no freezing)
Filter precision	40 micron
Working medium	Clean air (after 40 micron filtration)
Maximum inlet pressure	15 bar
Adjustable pressure range	1.5 to 9 bar

Materials

Body	Aluminium
Bowl	Polycarbonate