

Features

- **Portable Box Design**
– Compact and lightweight box for easy storage and access.
- **Contains 50 Durable Tags** – Includes 50 waterproof, tear-resistant tags ideal for various work environments.
- **Double-Sided Matte Surface** – Easy-to-write, scruff-resistant surface allows clear markings on both sides.
- **Indoor & Outdoor Use** – Designed to withstand harsh conditions without cracking, warping, or shrinking.
- **Writable & Customisable** – Ample space for date, signature, and important notes.
- **Disposable & Practical** – Simple, single-use solution for maintaining safety compliance at job sites.

RS PRO Lockout Tags in a Box (50)

RS Stock No.: 0694392



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Safety Tags in a Box is a portable and convenient safety management tool, designed to keep essential tags within reach at all times.*
- *Comes in a disposable, compact box that can be hung near workstations or lockout points.*
- *Contains 50 high-quality safety tags, suitable for use in both indoor and outdoor environments.*
- *Tags are waterproof, durable, and tear-resistant, maintaining integrity in tough industrial settings.*
- *Each tag offers ample writing space on both sides with a matte, scruff-resistant finish, making it easy to add important safety instructions, dates, or personnel details.*
- *A perfect solution for efficient, on-the-go lockout/tagout safety compliance and visual hazard communication.*
- *Suitable for both indoor and outdoor use.*

General Specifications

Type	Safety Tags-In-a-Box
Material	330 microns Synthetic Paper made from high-strength Polyester (PET) film
Colour	Red & White
Padlock holes	01
Package	BOPP + Box

Mechanical Specifications

Dimensions (Box Dimensions)	144mm x 85mm x 22mm
Height	144mm
Width	85mm
Depth	22mm
Dimensions (Tag Dimensions)	140mm x 80mm
Height	140mm
Width	80mm
Weight	88 Grams

Operation Environment Specifications

Withstand temperature	-20 °C to 80 °C
-----------------------	-----------------