

IN 32 19

Screwdriver bit socket 3/4"

for in-hex screws, long pattern

Code	ETIM
6276070	EC002157
EAN	UNSPSC
4010886627600	27-11-17-01
Country of origin	eCl@ss
Germany	21-04-04-02
Customs tariff number	
82079030	



Article description

- Acc. to DIN 7422
- Square drive as per DIN 3120 - D 20, ISO 1174, with locking pin
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated

Article information

Contents (Qty of pieces)	1	Drive connector square female [inch]	3/4"
Net weight [kg]	0,433 kg	Standard	DIN 7422 DIN 3120 - D 20 ISO 1174
Total length [mm]	80 mm	Width across flats l [mm]	19
Total width [mm]	38 mm	Backup	Locking pin
Surface	chrome-plated	Tip length	25,5 mm
Material	Chrome-vanadium steel	Insert Ø Actuator	38 mm
Drive connector square female (metric)	20,0 mm		