

23.6" LED Monitor

Art. no. TVAC10041

Page 1 of 3



- Full HD resolution: 1920 × 1080 pixels
- Fast response time (5 ms)
- LED background illumination: Superior colour display and contrast
- Graphical on-screen display (OSD)
- Connections: HDMI, VGA, 2 × BNC, 2 × cinch (audio), PC audio
- Integrated loudspeaker
- Low power consumption
- For wall and ceiling installation (with VESA mount)

The 23.6" LED monitor displays Full HD 1080p images in 16:10 format. This makes it suitable for displaying megapixel surveillance pictures, as well as use with HD SDI cameras (HDMI converter required). All settings can be conveniently made using the multilingual on-screen display (OSD).

Detailed surveillance pictures in Full HD

With its high resolution in HD1080p, outstanding picture fidelity and fast reaction time, the monitor produces accurate surveillance pictures. The LED backlighting ensures optimum contrast and an extremely realistic color display. The monitor is also equipped with two audio inputs, as well as automatic signal detection and a 3D comb filter for a softer and clearer image without the annoying dot-crawl effect.

Versatile connections

Four connections ensure great flexibility when connecting the monitor to recorders, cameras, etc. The HDMI connection makes the monitor perfect for displaying Full HD pictures. Another VGA connection as well as two BNC inputs provide additional options - which makes the monitor a suitable component for versatile surveillance systems.

Professional HD surveillance

Thanks to Full HD resolution (1920 x 1080 pixel), the monitor produces high resolution images for professional surveillance. Furthermore, high-quality industry components ensure the monitor operates reliably for 24/7 use. The efficient LED display ensures very low power consumption.

23.6" LED Monitor

Art. no. TVAC10041

Page 2 of 3

Easy installation

VESA standard mounts can be used to fix it to a wall or ceiling. This makes installation fast and easy.

Technical Data:

Dimensions	580 x 407 x 75 mm
Connections	1 x HDMI, 1x VGA, 2 x BNC, 1 x audio (3.5 mm jack), 2 x chinch audio, 2 x BNC-Out
Output	2 x BNC
Horizontal/vertical viewing angle	160° x 160° °
Picture format	16:10
Screen diagonal	23.6 "
Width	580 mm
Gross weight	6.2 kg
Display surface	matte
EAN	4043158053555
Input	1 x HDMI, 1 x VGA, 2 x BNC, 1 x audio (3.5mm jack), 2 x chinch audio
Color levels	16.7 MIO
Frequency range	30 – 80KHz (H) / 50 – 75Hz (V) GHz
Housing material	Plastic

Brightness	300 cd/m ²
Height	425 mm
Comb filter	3D
Contrast ratio	10.000:1
Loudspeaker	2 x 1,5 W
Power consumption	max. 25 W
Max. operating temperature	40 °C
Max. humidity	max. 85 %
Min. operating temperature	0 °C
Monitor type	LED
Net weight	4.4 kg
Pixel pitch	0.2715 x 0.2715 (H) x (V) mm
Reaction time	5 ms
Signal detection	Automatic
DC voltage supply	12 V
Power consumption	3.000 mA



Security Tech Germany

23.6" LED Monitor

Art. no. TVAC10041

Page 3 of 3

Video system	PAL / NTSC
--------------	------------