

FEATURES

- **Polyacrylic material:** Provides excellent resistance to chemicals and wear, ensuring durability.
- **Maximum operating pressure of 2000 kPa:** Suitable for high-pressure applications, enhancing safety and reliability.
- **Maximum operating temperature of 200 °C:** Capable of withstanding high temperatures, making it versatile for various environments.
- **Rotary speed of 10 m/s:** Supports efficient operation in dynamic systems.
- **11 mm section:** Offers a robust sealing solution for various gland and valve sizes.

RS PRO 8m Polyacrylic Gland Packing, 11mm Section

RS Stock No: 606-574



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland packing is designed for sealing applications in industrial environments. Made from durable polyacrylic material, it is ideal for use in high-pressure and high-temperature settings, ensuring reliable performance and longevity.

General Specifications

Maximum Operating Pressure	2000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	10 m/s
Section	11 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polyacrylic

Operation Environment Specifications

Maximum Operating Temperature	200 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------