

Autodry Rapid Hand Dryer

**Compact, high speed,
low energy hand dryer**

- 10 second drying time – saves time and energy
- High speed and low energy – reduces time taken to dry hands and washroom queues
- Robust die cast aluminium cover – ideal for heavy duty use
- Two heat settings for year round comfort

**Autodry rapid
dryer Vs
conventional
dryer... Annual
Saving £70.45
per unit**



Key Features

- Compact design to fit in small washrooms
- Two heat settings at installation to suit the temperature of the washroom heater on at 900W or heater off at 640W
- Automatic infra-red operation maintains hygiene
- Bright blue LED guides hand positioning when dryer is operating
- Available in white and chrome finishes
- Compact and robust die cast aluminium cover is ideal for heavy duty commercial use
- 2 year UK guarantee

Technical Specification

- Operating voltage – 220-240Vac, 50Hz, 650W (heater off), 900W (heater on)
- Air speed – 64 m/s
- Air output temperature – 77°F (25°C), ambient temperature 68°F (20°C)
- Motor type – 23,000 rpm, brush type, dual bearings
- 250W heater element
- Sensor range – 100mm
- Noise level – 76dB(A) @ 1m
- IP22 rated

Dimensions



Product Ref.	Finish	Model	Cat No.
Autodry Rapid	White	AEW1	66762001
Autodry Rapid	Chrome	AEC1	66762101

Usage based on 150 dries per day, 365 days per year. Costs based on £0.01 per paper towel and £0.12 per kWh. Standby time not included.