

MTS FLS RANGE

MTS TECH POWER FLS
S3S HI CI FO LG SR ESD



SAVE TIME AND HASSLE. WIN CONVENIENCE AND COMFORT.

MTS Tech Power leisure safety shoes offer a blend of protection, comfort, and style for those requiring protective footwear. Now featuring the Fast Lacing System (FLS), these shoes enhance convenience and safety for workers across various industrial settings, ensuring fast, easy to use, and reliable foot protection. What makes Fast Lacing System (FLS) different from other lacing options is its system that enables workers to adjust the way shoes fit with a simple twist, instead of the traditional way tying and untying shoelaces. This translates for wearers into benefits like time saving, reduced risks for injury, less frustration and enhanced focus on their work. Fast Lacing System (FLS) is the ultimate footwear solution for workers who value convenience, safety, comfort and durability.



MTS Tech Power Fast Lacing System (FLS)

FEATURES

- Suitable for Indoor / Outdoor use
- Ideal for: Logistics, Services, Warehousing and Transportation industries
- Composite toe cap protects against impact and compression
- Flexible and lightweight safety shoe, stylish design
- Water resistant full supple leather and CORDURA® material
- Fast Lacing System (FLS)
- Artico lining that provides the feeling of putting on a comfortable slipper
- Reflective piping on the heel area



Antistatic properties



Anti-puncture resistance
with PS level



Heel energy absorption



Slip Resistant (SR)



Fuel Oil Resistant (FO)



Heat Insulated Sole (HI)
Cold Insulated Sole (CI)



Ladder grip (LG)



ESD: Certification of
Electrical resistance

TECHNICAL SPECIFICATIONS

Upper	Water resistant full supple leather and CORDURA® material
Lining	ARTICO® black color, up to the toes, slipper feeling
Tongue	Bellows tongue in ON STEAM® microfibre, lining ARTICO® and padded with 10mm thick foam
Ankle support	CORDURA® material, ARTICO® lining and padded with 10 mm thick foam
Fastening	Fast Lacing System (FLS)
Toe cap	Ultralight and extra wide 200 Joules, Composite LIGHT SYSTEM®
Midsole	Composite FLEX SYSTEM®, anti-magnetic and thermal insulated
Insole	Thermoformed in active carbon dual density foam, antistatic, ESD and antibacterial FRESH TECH®
Sole	PU 2D, TECH SOLE® ankle anti-twist system, oil resistant FO, antistatic, HI-CI
Sole pattern	Multi-purpose cleated indoor/outdoor outsole, well-defined heel, cleated arch, SR standard
Weight (per shoe)	Approximately 600 g
Colors	Black upper and dark grey/light grey outsole
Sizes	35-48 (3-13 UK)
Standard	EN ISO 20345:2022 / EN 61340-5-1:2016
Style	Low cut

ORDERING INFORMATION

DESCRIPTION	REF. IN SAP	REF. IN EQUINOPS	SIZE
MTS Tech Power FLS	6270653	7080603	35-48

MTS
UNITED KINGDOM
Honeywell House, Skimped Hill Lane,
Bracknell, Berkshire RG12 1EB
Phone: +44 (0) 1256 274938
Email: info-uk.hsp@honeywell.com

ANNIC S.A.S.
1 rue des Usines
82250 Laguepie – France
Tel.: +33 (0) 563 302 101
Fax.: +33 (0) 563 314 018
Email: contact@mts-morethansafety.com

MTS
NORDIC AB
Box 15 147
SE-167 15 Bromma – Sverige
Phone: +46 (0) 424480433
Email: info-nordic.hsp@honeywell.com

For More Information
automation.honeywell.com

For Information on Innovations and Patents
hsmpats.com

MTS
BENELUX BV
Lange Amerikaweg 55
7332 BP Apeldoorn, Nederland
Tel: +31 (0) 20 5656 988
Email: info-benelux.hsp@honeywell.com

