

CAT. N° 0 019 57



## PACK OF 100 Ø25 MM ISO END CAPS FOR PLEXO<sup>3</sup> CABINETS

Pack (number of units)	1
Volume (dm <sup>3</sup> )	3,63
Weight (g)	524,00

### Product characteristics

#### Accessories

##### Direct piercing end caps

- Pack consisting of 100 Ø25 mm ISO end caps,

### General characteristics

#### Plexo<sup>3</sup> - IP 65 weatherproof cabinets, multifunction sleeves and accessories

- Self-extinguishing: resistance to incandescent wire 650°C.
- Allows to achieve assemblies conform to IEC 61 439 - 3
- Weatherproof cabinets - IP 65 - IK 09 - Class II
- Door and cabinet fully reversible. Removable chassis and faceplates from 2-row versions up
- 2-position rail for modular products and moulded cases. Spacing between rails 150 mm
- Can be fitted with perforated plates and solid faceplates for mounting non-modular products
- Lockable door handle, sealable cover and faceplate
- Shock-resistant polystyrene material
- Box colour light grey L750A, cover colour dark grey R746A
- Supplied without terminal blocks

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.286\)](#)
- [Technical page \(p.287\)](#)



#### Installation & technical data

- [EXB14046\\_CA\\_Plexo3\\_EN\\_print](#)