

C55PB-PRO/7
Workstation for workshop equipment combination RSC55

Composed of:

C55B

Workbench with worktop (2050x700 mm) covered with a shockproof, nonscratch ABS coat resistant to oils and hydrocarbons.

Fitted with:

- Holes for a vice (1599F/150 - 1599GI/150, to be ordered separately)
- Vertically adjustable feet

C55M7

Fixed module with seven drawers (588x367 mm) with ball bearing slides

- Aluminium opening system throughout length of drawer
- Drawer bases protected by foamed rubber mats
- Front centralized lock
- Can be fitted with thermoformed trays

C55MS

Fixed service module

- Built-in waste bin
- Paper roll compartment
- Storage drawer, 305x270 mm

C55/2PM + C55/PF

Tool wall system with 2 suspended cabinets

- 2 suspended cabinets, 1024x400x300 mm, with gas springs
- 2 under-cabinet panels, 1024x620x25mm
- 2 under-cabinet perforated tool panels, 1024x620x25 mm

 350 kg



	 art.	art.
	055000065	C55PB-PRO/7