



**29251730**

2517 - Taper bushes

**2D Technical Drawing**

**Dynamic 3D View**
**Technical Specifications**

<b>TYPE (TYPE)</b>	2517
<b>Ø D1 (D1) mm</b>	85.5
<b>Part number (CODE)</b>	29251730
<b>Design (EXEC)</b>	A
<b>L (L) mm</b>	45
<b>Ø D2 H8 only prebore (D2S)</b>	-
<b>Ø D2 with ISO G7 hole, DIN 6885-JS9 slot (D2CF)</b>	30
<b>keyway width (B) mm</b>	8
<b>keyway depth (T2) mm</b>	3.3
<b>British Standard Whitworth (SCREWS)</b>	1/2"x1"
<b>Tightening torque (TT) N/m</b>	48
<b>Weight (WEIGHT) kg</b>	1.49
<b>Material (MAT)</b>	Gray cast iron