



Leiterquerschnitt/ *wire gauge* : 2,5mm<sup>2</sup> /AWG14

Oberfläche/ *surface* : Gold Tec (NiP+Au)

 All Dimensions in mm Original Size DIN A 4		Techn. Character.			Nicht tolerierte Masse/ <i>Free size tolerances</i>	
			Dat.	Name	Massstab/ <i>Scale</i>  5:1	Han E-Kontaktbuchse-c <i>Han E-female contact</i>
		Detail.	14.05.04	Ste		
		Insp.		KR		
		Stand.				
411022		HARTING Electric GmbH & Co. KG				TB 09 33 000 6402
Mod.	Dat.	Name	D-32339 Espelkamp			
					Sub.	Blatt/ <i>page</i>