



Part Number : [734151000](#)

Product Description : MMCX Jack, Right-Angle, PCB Receptacle, Through Hole, Brass Body, Gold (Au) Plated, Tray, 50 Ohms

Series Number : 73414

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[734151000 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73414
Description	MMCX Jack, Right-Angle, PCB Receptacle, Through Hole, Brass Body, Gold (Au) Plated, Tray, 50 Ohms
Product Name	MMCX
Style	PCB
Type	Microminiature
UPC	800756000015

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	0.436/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A

PCB Mounting	Through Hole
PCB Thickness - Recommended	2.79mm
Reverse Polar	No
Wire/Cable Type	N/A

This document was generated on Aug 04, 2025