

## Metric Size - TU TU0425R1-100

### Datasheet

#### General series information

- Applicable tubing O.D.: Ø 2 to Ø 16 mm
- Operating temperature: -20 to 60 °C
- 29 colour variations.

#### Standard specifications

|                                  |                                            |
|----------------------------------|--------------------------------------------|
| Size                             | 0425 (O.D. Ø4 I.D. Ø2.5)                   |
| Color                            | R1 (Red, Solid)                            |
| Roll Length                      | 100 m                                      |
| Reel Length                      | None                                       |
| Suffix                           | None                                       |
| Pressure medium                  | Air, Water                                 |
| Maximum ambient temperature      | 60 °C / 40 °C for Water                    |
| Minimum ambient temperature      | -20 °C (with no freezing) / 0 °C for Water |
| Number of pneumatic connections  | 2 pcs.                                     |
| Max. operating pressure at 20 °C | 0.8 MPa                                    |
| Weight                           | 0.800 Kg                                   |

## Additional information

Catalogue

[TU-29COLOR-A\\_EU.pdf](#)