

LONG LIFE DRILLING IN REINFORCED CONCRETE

PRO SDS plus-5X

PRO

- 1 High-quality, tough tungsten carbide ensures strength and durability
- 2 4-cutter head doesn't jam or break when you hit rebar
- 3 4-flute design for efficient dust reduction



PRO SDS plus-5X Hammer Drill Bit

PRO



- ▶ For efficient drilling in concrete and reinforced concrete, eg during installation work, including electrical installation, or other internal fittings
- ▶ Highly efficient for interior construction workers, electricians, plumbers, and HVAC installers: Long Life
- ▶ Lasts up to 1.5x longer than a Bosch SDS plus-1 Drill Bit
- ▶ Fits all SDS plus rotary hammers



PRODUCT PROPERTIES						ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Diameter (D) Inch	Working length Inch	Total length Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
Pack of 1 packed without shrink sleeve										
3	50	100	-	-	-	P2e	1	5	4059952676722	2 608 707 226
3	100	160	-	-	-	P2e	1	5	4059952676739	2 608 707 227
3.5	50	110	-	-	-	P2e	1	5	4059952676746	2 608 707 228
3.5	100	160	-	-	-	P2e	1	5	4059952676753	2 608 707 229

PRO SDS plus-5X Hammer Drill Bit

PRO

PRODUCT PROPERTIES						ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Diameter (D) Inch	Working length Inch	Total length Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
4	50	110	-	-	-	P2e	1	5	6949509227461	2 608 836 604
4	100	160	-	-	-	P2e	1	5	6949509227478	2 608 836 605
5	50	110	-	-	-	P2e	1	10	6949509223241	2 608 833 771
5	100	160	-	-	-	P2e	1	10	6949509223258	2 608 833 772
5	150	210	-	-	-	P2e	1	5	6949509223265	2 608 833 773
5	200	260	-	-	-	P2e	1	5	6949509227485	2 608 836 606
5	250	310	-	-	-	P2e	1	5	6949509227492	2 608 836 607
5	400	460	-	-	-	P2e	1	5	6949509227508	2 608 836 608
5.5	50	110	-	-	-	P2e	1	10	6949509223272	2 608 833 774
5.5	100	160	-	-	-	P2e	1	5	6949509223289	2 608 833 775
5.5	150	210	-	-	-	P2e	1	1	6949509223296	2 608 833 776
5.5	200	260	-	-	-	P2e	1	5	6949509227515	2 608 836 609
5.5	250	310	-	-	-	P2e	1	5	6949509227522	2 608 836 610
5.5	400	460	-	-	-	P2e	1	5	6949509227539	2 608 836 611
6	50	110	-	-	-	P2e	1	10	6949509223302	2 608 833 777
6	100	160	-	-	-	P2e	1	10	6949509223319	2 608 833 778
6	150	210	-	-	-	P2e	1	10	6949509223326	2 608 833 779
6	200	260	-	-	-	P2e	1	10	6949509223333	2 608 833 780
6	250	310	-	-	-	P2e	1	5	6949509227546	2 608 836 612
6	400	460	-	-	-	P2e	1	5	6949509227553	2 608 836 613
6.5	400	465	-	-	-	P2e	1	1	4059952676784	2 608 707 232
6.5	50	110	-	-	-	P2e	1	10	6949509223340	2 608 833 781
6.5	100	160	-	-	-	P2e	1	10	6949509223357	2 608 833 782
6.5	150	210	-	-	-	P2e	1	5	6949509223364	2 608 833 783
6.5	200	260	-	-	-	P2e	1	5	6949509223371	2 608 833 784
6.5	250	310	-	-	-	P2e	1	5	6949509227560	2 608 836 614
7	250	315	-	-	-	P2e	1	1	4059952676791	2 608 707 233
7	400	465	-	-	-	P2e	1	1	4059952676807	2 608 707 234
7	50	110	-	-	-	P2e	1	10	6949509223388	2 608 833 785
7	100	160	-	-	-	P2e	1	10	6949509223395	2 608 833 786
7	150	210	-	-	-	P2e	1	5	6949509223401	2 608 833 787
7	200	260	-	-	-	P2e	1	5	6949509227577	2 608 836 615
8	50	110	-	-	-	P2e	1	10	6949509223418	2 608 833 788
8	100	160	-	-	-	P2e	1	10	6949509223425	2 608 833 789
8	150	210	-	-	-	P2e	1	10	6949509223432	2 608 833 790
8	200	260	-	-	-	P2e	1	10	6949509223449	2 608 833 791
8	250	310	-	-	-	P2e	1	5	6949509223456	2 608 833 792
8	300	360	-	-	-	P2e	1	5	6949509223463	2 608 833 793
8	400	460	-	-	-	P2e	1	5	6949509223470	2 608 833 794
8	550	610	-	-	-	P2e	1	1	6949509227584	2 608 836 616
8.5	100	165	-	-	-	P2e	1	5	4059952676814	2 608 707 235
8.5	150	215	-	-	-	P2e	1	5	4059952676821	2 608 707 236
8.5	200	265	-	-	-	P2e	1	1	4059952676838	2 608 707 237
9	200	265	-	-	-	P2e	1	1	4059952676845	2 608 707 238
9	100	160	-	-	-	P2e	1	5	6949509223487	2 608 833 795
9	150	210	-	-	-	P2e	1	5	6949509223494	2 608 833 796
9.5	100	160	-	-	-	P2e	1	5	6949509227591	2 608 836 617
10	950	1,000	-	-	-	P2e	1	1	4059952697871	2 608 707 249
10	50	110	-	-	-	P2e	1	10	6949509223500	2 608 833 797
10	100	160	-	-	-	P2e	1	10	6949509223517	2 608 833 798
10	150	210	-	-	-	P2e	1	10	6949509223524	2 608 833 799
10	200	260	-	-	-	P2e	1	10	6949509223531	2 608 833 800
10	250	310	-	-	-	P2e	1	5	6949509223548	2 608 833 801
10	300	360	-	-	-	P2e	1	5	6949509223555	2 608 833 802
10	400	460	-	-	-	P2e	1	5	6949509223562	2 608 833 803
10	550	610	-	-	-	P2e	1	1	6949509227607	2 608 836 618
11	100	160	-	-	-	P2e	1	5	6949509223579	2 608 833 804
11	150	210	-	-	-	P2e	1	1	6949509223586	2 608 833 805
11	200	260	-	-	-	P2e	1	5	6949509223593	2 608 833 806
12	950	1,000	-	-	-	P2e	1	1	4059952697888	2 608 707 250
12	100	160	-	-	-	P2e	1	10	6949509223609	2 608 833 807
12	150	210	-	-	-	P2e	1	10	6949509223616	2 608 833 808
12	200	260	-	-	-	P2e	1	10	6949509223623	2 608 833 809
12	250	310	-	-	-	P2e	1	5	6949509223630	2 608 833 810
12	300	360	-	-	-	P2e	1	5	6949509223647	2 608 833 811
12	400	460	-	-	-	P2e	1	5	6949509223654	2 608 833 812

PRO SDS plus-5X Hammer Drill Bit

PRO

PRODUCT PROPERTIES						ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Diameter (D) Inch	Working length Inch	Total length Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
12	550	610	-	-	-	P2e	1	1	6949509227614	2 608 836 620
12.7	100	160	-	-	-	P2e	1	5	6949509227621	2 608 836 622
13	100	160	-	-	-	P2e	1	5	6949509223661	2 608 833 813
13	150	210	-	-	-	P2e	1	1	6949509223678	2 608 833 814
13	200	260	-	-	-	P2e	1	5	6949509223685	2 608 833 815
14	950	1,000	-	-	-	P2e	1	1	4059952697895	2 608 707 251
14	100	160	-	-	-	P2e	1	10	6949509223692	2 608 833 816
14	150	210	-	-	-	P2e	1	10	6949509223708	2 608 833 817
14	200	260	-	-	-	P2e	1	10	6949509223715	2 608 833 818
14	250	310	-	-	-	P2e	1	5	6949509223722	2 608 833 819
14	300	360	-	-	-	P2e	1	5	6949509223739	2 608 833 820
14	400	460	-	-	-	P2e	1	5	6949509223746	2 608 833 821
14	550	610	-	-	-	P2e	1	1	6949509227638	2 608 836 623
14.3	100	160	-	-	-	P2e	1	5	6949509227645	2 608 836 625
15	100	160	-	-	-	P2e	1	5	6949509223753	2 608 833 822
15	200	260	-	-	-	P2e	1	5	6949509223760	2 608 833 823
15	400	460	-	-	-	P2e	1	1	6949509223777	2 608 833 824
16	950	1,000	-	-	-	P2e	1	1	4059952697901	2 608 707 252
16	150	210	-	-	-	P2e	1	10	6949509223784	2 608 833 825
16	200	260	-	-	-	P2e	1	5	6949509223791	2 608 833 826
16	250	310	-	-	-	P2e	1	5	6949509223807	2 608 833 827
16	300	360	-	-	-	P2e	1	5	6949509223814	2 608 833 828
16	400	460	-	-	-	P2e	1	5	6949509223821	2 608 833 829
16	550	610	-	-	-	P2e	1	1	6949509227652	2 608 836 626
17	400	465	-	-	-	P2e	1	1	4059952676852	2 608 707 239
17	150	210	-	-	-	P2e	1	5	6949509227669	2 608 836 628
17	250	310	-	-	-	P2e	1	5	6949509227676	2 608 836 629
17.5	100	160	-	-	-	P2e	1	5	6949509227683	2 608 836 630
18	950	1,000	-	-	-	P1e	1	1	4059952697918	2 608 707 253
18	150	200	-	-	-	P2e	1	5	6949509227690	2 608 836 631
18	250	300	-	-	-	P2e	1	1	6949509227706	2 608 836 632
18	400	450	-	-	-	P2e	1	1	6949509227713	2 608 836 633
18	550	600	-	-	-	P2e	1	1	6949509227720	2 608 836 634
19	150	200	-	-	-	P2e	1	5	6949509227737	2 608 836 636
19	250	300	-	-	-	P2e	1	1	6949509227744	2 608 836 637
19	400	450	-	-	-	P2e	1	1	6949509227751	2 608 836 638
20	950	1,000	-	-	-	P1e	1	1	4059952697925	2 608 707 254
20	150	200	-	-	-	P2e	1	5	6949509227768	2 608 836 639
20	250	300	-	-	-	P2e	1	1	6949509227775	2 608 836 640
20	400	450	-	-	-	P2e	1	1	6949509227782	2 608 836 641
20	550	600	-	-	-	P2e	1	1	6949509227799	2 608 836 642
22	950	1,000	-	-	-	P1e	1	1	4059952697932	2 608 707 255
22	200	250	-	-	-	P2e	1	5	6949509227805	2 608 836 644
22	400	450	-	-	-	P2e	1	1	6949509227812	2 608 836 645
22	550	600	-	-	-	P2e	1	1	6949509227829	2 608 836 646
24	200	250	-	-	-	P2e	1	1	6949509227836	2 608 836 647
24	400	450	-	-	-	P2e	1	1	6949509227843	2 608 836 648
25	550	600	-	-	-	P1e	1	1	4059952676869	2 608 707 240
25	950	1,000	-	-	-	P1e	1	1	4059952697949	2 608 707 256
25	200	250	-	-	-	P2e	1	1	6949509227850	2 608 836 649
25	400	450	-	-	-	P2e	1	1	6949509227867	2 608 836 650
26	200	250	-	-	-	P2e	1	1	6949509227874	2 608 836 651
26	400	450	-	-	-	P2e	1	1	6949509227881	2 608 836 652
28	200	250	-	-	-	P1e	1	1	4059952676876	2 608 707 241
28	400	450	-	-	-	P1e	1	1	4059952676883	2 608 707 242
30	200	250	-	-	-	P1e	1	1	4059952676890	2 608 707 243
30	400	450	-	-	-	P1e	1	1	4059952676906	2 608 707 244
32	400	450	-	-	-	P1e	1	1	4059952676913	2 608 707 245
Pack of 10										
5	50	110	-	-	-	P1h	10	1	6949509223838	2 608 833 889
5	100	160	-	-	-	P1h	10	1	6949509223845	2 608 833 890
5.5	50	110	-	-	-	P1h	10	1	4059952676760	2 608 707 230
5.5	100	160	-	-	-	P1h	10	1	4059952676777	2 608 707 231
6	50	110	-	-	-	P1h	10	1	6949509223852	2 608 833 891
6	100	160	-	-	-	P1h	10	1	6949509223869	2 608 833 892
6	150	210	-	-	-	P1h	10	1	6949509223876	2 608 833 893

PRO SDS plus-5X Hammer Drill Bit

PRO

PRODUCT PROPERTIES						ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Diameter (D) Inch	Working length Inch	Total length Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
6.5	100	160	-	-	-	P1h	10	1	6949509223883	2 608 833 894
6.5	150	210	-	-	-	P1h	10	1	6949509223890	2 608 833 895
6.5	200	260	-	-	-	P1h	10	1	6949509223906	2 608 833 896
7	100	160	-	-	-	P1h	10	1	6949509223913	2 608 833 897
8	50	110	-	-	-	P1h	10	1	6949509223920	2 608 833 898
8	100	160	-	-	-	P1h	10	1	6949509223937	2 608 833 899
8	150	210	-	-	-	P1h	10	1	6949509223944	2 608 833 900
8	200	260	-	-	-	P1h	10	1	6949509223951	2 608 833 901
10	100	160	-	-	-	P1h	10	1	6949509223968	2 608 833 902
10	150	210	-	-	-	P1h	10	1	6949509223975	2 608 833 903
10	200	260	-	-	-	P1h	10	1	6949509223982	2 608 833 904
12	100	160	-	-	-	P1h	10	1	6949509223999	2 608 833 905
12	150	210	-	-	-	P1h	10	1	6949509224002	2 608 833 906
12	200	260	-	-	-	P1h	10	1	6949509224019	2 608 833 907
14	100	160	-	-	-	P1h	10	1	6949509224026	2 608 833 908
16	150	210	-	-	-	P1h	10	1	6949509224033	2 608 833 909

PRO SDS plus-5X Hammer Drill Bit Set

PRO



- ▶ For efficient drilling in concrete and reinforced concrete, eg during installation work, including electrical installation, or other internal fittings
- ▶ Highly efficient for interior construction workers, electricians, plumbers, and HVAC installers: Long Life
- ▶ Lasts up to 1.5x longer than a Bosch SDS plus-1 Drill Bit
- ▶ Fits all SDS plus rotary hammers



PRODUCT PROPERTIES				ORDERING INFORMATION				
Diameter mm	Working length mm	Total length mm	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number	
6	100	160	P1h	3	10	6949509224064	2 608 833 912	
8	100	160						
10	100	160						
5	50	110	P1h	5	5	6949509224040	2 608 833 910	
6	50	110						
6	100	160						
8	100	160						
10	100	160						
5.5	50	110	P1a	5	5	3165140941457	2 608 837 138	
6	50	110						
7	100	160						
8	100	160						
10	100	160						
6	100	160	P1h	5	5	6949509224057	2 608 833 911	
6	100	160						
8	100	160						
8	100	160						
10	100	160						
5	50	115	P1k	7	1	4059952676920	2 608 707 246	
6	50	115						
8	50	115						
6	100	165						
8	100	165						
10	100	165						
12	100	165						