

# Spec-Kon® cable ties

## The right cable tie for the right application

### Characteristics


A complete range of cable ties for control panel applications.

- Available in different packaging quantities to respond to the user's need
- Available in different lengths and tensile strengths
- Sophisticated, ergonomic fastening installation tools and easy to use cable ties dispenser

### Technical Information

Material	Polyamide 6.6
Temperature range	-40°C to +85°C
Colour	Natural
Flammability rating	UL 94 V-2
Other properties	Halogen free, Silicone free

Product Ref.	Length L	Width W	Min. tensile strength	Bundle Dia. from... to...	Quantity	Bags/ Carton
	[mm]	[mm]				
SKT100-80-100	100	2,5	80	1,5 - 22	100	550
SKT100-80	100	2,5	80	1,5 - 22	1000	70
SKT140-80-100	140	2,5	80	1,5 - 33	100	450
SKT140-80	140	2,5	80	1,5 - 33	1000	55
SKT160-80-100	160	2,5	80	1,5 - 40	100	400
SKT160-80	160	2,5	80	1,5 - 40	1000	45
SKT200-80-100	200	2,5	80	1,5 - 53	100	300
SKT200-80	200	2,5	80	1,5 - 53	1000	32
SKT140-180-100	140	3,6	180	2 - 33	100	300
SKT140-180	140	3,6	180	2 - 33	1000	30
SKT200-180-100	200	3,6	180	2 - 53	100	200
SKT200-180	200	3,6	180	2 - 53	1000	22
SKT300-180-100	300	3,6	180	2 - 76	100	120
SKT300-180	300	3,6	180	2 - 76	1000	12
SKT370-180-100	370	3,6	180	2 - 102	100	120
SKT370-180	370	3,6	180	2 - 102	1000	12
SKT188-220-100	188	4,8	220	3 - 46	100	160
SKT188-220	188	4,8	220	3 - 46	1000	16
SKT250-220-100	250	4,8	220	3 - 60	100	120
SKT250-220	250	4,8	220	3 - 60	1000	12
SKT300-220-100	300	4,8	220	3 - 76	100	80
SKT300-220	300	4,8	220	3 - 76	1000	8
SKT370-220-100	370	4,8	220	3 - 102	100	70
SKT370-220	370	4,8	220	3 - 102	1000	7
SKT300-540-100	300	7,6	540	7 - 76	100	50
SKT300-540	300	7,6	540	7 - 76	500	10
SKT370-540-100	370	7,6	540	7 - 102	100	40
SKT370-540	370	7,6	540	7 - 102	500	8
SKT750-540-50	750	7,6	540	7 - #N/A	50	30
SKT776-780-50	776	9,0	780	7 - 228	50	30
SKT912-780-50	912	9,0	780	7 - 263	50	10



# Spec-Kon® cable ties

## The right cable tie for the right application

### Characteristics

A complete range of cable ties for control panel applications.

- Available in different packaging quantities to respond to the user's need
- Available in different lengths and tensile strengths
- Sophisticated, ergonomic fastening installation tools and easy to use cable ties dispenser

### Technical Information

Material	Polyamide 6.6
Temperature range	-40°C to +85°C
Colour	UV-resistant black
Flammability rating	UL 94 V-2
Other properties	UV-resistant, Halogen free, Silicone free

Product Ref.	Length L [mm]	Width W [mm]	Min. tensile strength [N]	Bundle Dia. from... to... [mm]	Quantity [pieces]	Bags/ Carton
SKT100-80X-100	100	2,5	80	1,5 - 22	100	550
SKT100-80X	100	2,5	80	1,5 - 22	1000	70
SKT140-80X-100	140	2,5	80	1,5 - 33	100	450
SKT140-80X	140	2,5	80	1,5 - 33	1000	55
SKT160-80X-100	160	2,5	80	1,5 - 40	100	400
SKT160-80X	160	2,5	80	1,5 - 40	1000	45
SKT200-80X-100	200	2,5	80	1,5 - 53	100	300
SKT200-80X	200	2,5	80	1,5 - 53	1000	32
SKT140-180X-100	140	3,6	180	2 - 33	100	300
SKT140-180X	140	3,6	180	2 - 33	1000	30
SKT200-180X-100	200	3,6	180	2 - 53	100	200
SKT200-180X	200	3,6	180	2 - 53	1000	22
SKT300-180X-100	300	3,6	180	2 - 76	100	120
SKT300-180X	300	3,6	180	2 - 76	1000	12
SKT370-180X-100	370	3,6	180	2 - 102	100	120
SKT370-180X	370	3,6	180	2 - 102	1000	12
SKT188-220X-100	188	4,8	220	3 - 46	100	160
SKT188-220X	188	4,8	220	3 - 46	1000	16
SKT250-220X-100	250	4,8	220	3 - 60	100	120
SKT250-220X	250	4,8	220	3 - 60	1000	12
SKT300-220X-100	300	4,8	220	3 - 76	100	80
SKT300-220X	300	4,8	220	3 - 76	1000	8
SKT300-540X-100	300	7,6	540	7 - 76	100	50
SKT300-540X	300	7,6	540	7 - 76	500	10
SKT370-540X-100	370	7,6	540	7 - 102	100	40
SKT370-540X	370	7,6	540	7 - 102	500	8
SKT750-540X-50	750	7,6	540	7 - #N/A	50	30
SKT776-780X-50	776	9,0	780	7 - 228	50	30
SKT912-780X-50	912	9,0	780	7 - 263	50	10

