

Model No. 429

Dual Jaw Clearance Aluminum Lockout Hasp, 1in (25mm) and 1-1/2in (38mm) Jaw Clearance

Best Used For:



Lockout Tagout



Group Lockout



Safety Lockout/Tagout

Overview & Features

Product Features

- Aluminum Lockout Hasp
- Lockout by multiple workers at each lockout point
- Keeps equipment inoperative while repairs or adjustments are being made
- Control cannot be turned on until last worker"s safety padlock is removed from hasp
- Dual jaw, spark resistant aluminum
- Dimensions are 2in x 5-7/8in (50mm x 149mm) with 1in x 1-1/2in (25mm x 38mm) inside jaw diameter, holds up to 8 safety padlocks

Product Details

The Master Lock No. 429 Aluminum Lockout Hasp features a dual jaw, spark resistant aluminum body with a 1in (25mm) and 1-1/2in (38mm) diameter inside jaw clearance, and can accept up to 8 padlocks. Ideal for lockout by multiple workers at each lockout point, the hasp keeps equipment inoperative while repairs or adjustments are made. Control cannot be turned on until last worker’s padlock is removed from hasp.

Product Specifications

Product Number	429
Lockout Hasp Length	150 mm
Accepts Shackle Diameter up to	7 mm
Colour	Silver
Description	Commercial Bagged
Shelf Pack Qty	12
Master Carton Qty	72

Master Lock Europe S.A.S.
10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu