

RLP73N2AR10FTDF

✓ ACTIVE

CGS | CGS RLP73

TE Internal #: 2176053-8

.1 ohm, Surface Mount Low Ohmic Resistor, Thick Film, 0805, .25 W,
1 %, ±300 ppm/°C, Solder, 2 Terminations, .55 mm [.022 in] Height,
CGS RLP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense



Resistance Value: .1 Ω
Resistor Type: Low Ohmic Resistor
Element Type: Thick Film
Package Size Code: 0805
Power Rating: .25 W

[All Thick Film Resistor: Current Sense \(190\)](#)

Features

Product Type Features

Resistor Type	Low Ohmic Resistor
Element Type	Thick Film
Package Size Code	0805

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Resistance Value	.1 Ω
Power Rating	.25 W
Resistance Class	Up to 1k Ω
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	2 mm[.079 in]



Product Width	1.25 mm[.049 in]
---------------	------------------

Usage Conditions

Temperature Coefficient	±300 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RLP73N2AR10FTDF

.1 ohm, Surface Mount Low Ohmic Resistor, Thick Film, 0805, .25 W, 1 %, ±300 ppm/°C, Solder, 2 Terminations, .55 mm [.022 in] Height, CGS RLP73



TE Part # 2176050-8
RLP73N 1E R10 5% 5K RL

TE Part # CAT-C339-R529A
Thick Film Resistor: Current Sense

Also in the Series | CGS RLP73

Surface Mount Resistors(337)

Customers Also Bought

TE Part #T1319100125-000
H10A-TS-M25

TE Part #1-2364686-8
AVH22 FLT SS LK RNG BLU 12V16A

TE Part #1676372-2
RN 0805 53R6 0.1% 10PPM 1KRL

TE Part #9-1879208-8
CPF0402 130K 0.1% 25PPM 5K RL

TE Part #2176331-7
CRGP 2512 33R 1%

TE Part #20009605-15
FX293X-100A-0100-L

TE Part #T4140512031-000
M12,REAR MOUNTING,MALE,D CODE,3P

TE Part #CAT-C73765-M1E
M12 Field Installable Unshielded

TE Part #ANT-433-CW-HW-SMA
Antenna 1/4 Wave Whip 433MHz SMA



Documents

Product Drawings

RLP73N 2A R10 1% 1K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2176053-8_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2176053-8_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2176053-8_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Low Ohmic Current Sense Resistors - Type RL73 Series

English