

MCC-MT 0,2-0,35 (0,0) BA - Crimp contact



1923717
<https://www.phoenixcontact.com/gb/products/1923717>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Female contact, is inserted into the plug after crimping the conductor, for the module plug housing MCC 1...-STZ-3,81 and MCC 1...-STZF-3,81, for cross sections of 0.2 mm² to 0.34 mm²

Commercial data

Item number	1923717
Packing unit	8,000 pc
Minimum order quantity	8,000 pc
Sales key	AABCAD
Product key	AABCAD
Catalog page	Page 827 (C-1-2013)
GTIN	4017918571450
Weight per piece (including packing)	0.44 g
Weight per piece (excluding packing)	0.5 g
Customs tariff number	85366990
Country of origin	DE

MCC-MT 0,2-0,35 (0,0) BA - Crimp contact



1923717

<https://www.phoenixcontact.com/gb/products/1923717>

Technical data

Product properties

Product type	Crimp contact
Product family	MCC-MT
Pitch	0 mm

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Stripping length of the individual wire	4 mm
Stripping length	4 mm ... 4.1 mm
Conductor cross section flexible	0.2 mm ² ... 0.34 mm ²
Conductor cross section AWG	24 ... 22

Material specifications

Contact surface	Tin Sn
Contact surface material	Tin
Metal surface contact area (top layer)	Tin Sn)

Dimensions

Dimensional drawing	
Pitch	0 mm

Electrical properties

Nominal current I_N	4 A
-----------------------	-----

Packaging specifications

Dimensional drawing	
Type of packaging	Belt
ESD level	(D) electrostatically conductive
Specification	DIN EN 61340-5-1 (VDE 0300-5-1): 2008-07


MCC-MT 0,2-0,35 (0,0) BA - Crimp contact

1923717

<https://www.phoenixcontact.com/gb/products/1923717>

Drawings

Dimensional drawing



MCC-MT 0,2-0,35 (0,0) BA - Crimp contact



1923717

<https://www.phoenixcontact.com/gb/products/1923717>

Classifications

ECLASS

ECLASS-13.0	27460403
-------------	----------

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

MCC-MT 0,2-0,35 (0,0) BA - Crimp contact



1923717

<https://www.phoenixcontact.com/gb/products/1923717>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.013 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk