



KR DIN 10-8

E0812790

Cable Lug KR DIN, 10mm², M8



Product Properties:

| | |
|--------------------------------|-------------------|
| Suitable for Class 2 conductor | Yes |
| Suitable for Class 5 conductor | Yes |
| Insulated | No |
| Number of mounting holes | 1 . |
| Flange shape | Ring shape |
| Colour insulation | Other |
| Slender flange model | No |
| With sight-hole | No |
| Conductor category | Several |
| Surface protection | Tinned |
| Material | Copper |
| Connecting angle | 180° (horizontal) |

Dimensions:

| | |
|----|--------|
| HS | 8.4 mm |
| ID | 4.5 mm |
| OD | 6 mm |
| T | 1 mm |
| P1 | 10 mm |
| P2 | 11 mm |
| L | 40 mm |
| N | 10 mm |

| | |
|--------------------------------|--------------------|
| W | 13 mm |
| MOQ | 100 . |
| Unit | pcs |
| Bolt dimension (metric) | 8 . |
| Nominal cross section | 10 mm ² |

Approvals:

| | |
|-----------------------------------|-----|
| Approved according to CE | Yes |
| Approved according to UKCA | Ja |

Compliance:

| | |
|--------------------------|-------------------------------|
| Conflict Minerals | Contain "Tin" |
| Extended Minerals | Contain "Copper" |
| PFAS | No PFAS |
| REACH | No SVHC (Latest. 05 Nov 2025) |
| RoHS | RoHS 3 (2015/863) |
| SCIP | Not Applicable |

Other information:

| | |
|---------------------------|---|
| ETIM-Class | EC001051 - Tube cable lug for copper conductors |
| ETIM-Release | 9.0 |
| Trademark | NEMIQ |
| Product Group | Cable lugs |
| Search Description | SKH2023ERIK2, ENR2025V, NYB04 |
| Alternative SKU | KRDIN10-8 |
| E-no | E0812790 |

Logistic information:

| | |
|--------------------------|--|
| Barcode | 733117641257 |
| Country of origin | CN |
| E-no | E0812790 |
| Item status | Stock item, normally in stock with reservation for in between sales. |
| MOQ | 100 . |
| Stock code | KRDIN 10-8 |
| Taric code | 85369010 |
| Unit | pcs |

*We reserve the right to make technical changes and disclaim any typographical errors.