



ENGLISH

Datasheet

Stock No: 452-625

RS Pro 3 Way Fused Terminal Block, 10A 250 V, Screw Down, Nylon



Product Details

Fused Polyamide

Inline fuseholder with pull-up latch for easy fuse replacement

White Colour

Secured with a screw and serrated washer fixing through the base of the earth terminal. Inserts are tinned brass

Specifications:

Mounting Type	Screw Down
Number of Ways	3
Termination Method	Screw Down
Material	Nylon
Cable CSA	6mm ²
Fuse Size	5 x 20mm
Current Rating	10A
Voltage Rating	250 V
Maximum Operating Temperature	+100°C