

PREVOST FILTRATION - SINGLE UNITS

Regulator



Part number	Female thread	Flow rate at 6.00 bar (l/min) ($\Delta P = 1.00$ bar)	Max. operating pressure (bar)	Net weight (Kg)
ATU R10100	G1/8	750.00	15.00	0,339
ATU R10101	G1/4	1500.00	15.00	0,339
ATU R10102	G3/8	4300.00	15.00	0,926
ATU R10103	G1/2	4700.00	15.00	0,926

