



Foot protection

ARONA S1P SRC Black

MANUFACTURING

Lightweight and flexible high cut shoe, for all-day comfort



Specific benefits



Comfort

- Shock-absorbing heel to relieve joint strain
- Dual-density outsole
- Flexible sole to reduce fatigue during use
- Lightweight product to reduce fatigue throughout the day



Performance

- High stability ensured by the sole's grip properties



Hygiene

- Removable insock for easy cleaning

Certifications and norms



EN ISO 20345

S1P FO A E SRC

Applications

- **Finishing works / Craftsmanship**
- **Events & scenic**
- **Light industry**
- **Maintenance**
- **Temporary work**
- **Public services**

Protects against risks



Antistatic



Shock



Slip



Perforation



Foot protection

ARONA S1P SRC Black

MANUFACTURING

Lightweight and flexible high cut shoe, for all-day comfort

Standards - Details

Technical details

Shoe type	High shoe
Outsole material	PU
Anti-perforation insert	Stainless steel
Upper material	Textile
Safety toe-cap	Stainless steel
Footbed material	EVA, Polyester
Footbed characteristic	Removable, Breathable, Pre-molded
Outsole finition	Injected
Weight (g per shoe)	486
Size range	35 → 48



ARONA S1P SRC

MANUFACTURING

Lightweight and flexible high cut shoe, for all-day comfort

Safety footwear

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
ARONASPBE35	Beige	35	ARONA S1P SRC	3295249231910	13295249231917	10	1	11.6 kg	59.5 cm	41.5 cm	33.0 cm
ARONASPBE36	Beige	36	ARONA S1P SRC	3295249232672	13295249232679	10	1	11.6 kg	59.5 cm	41.5 cm	33.0 cm
ARONASPBE37	Beige	37	ARONA S1P SRC	3295249232689	13295249232686	10	1	11.6 kg	59.5 cm	41.5 cm	33.0 cm
ARONASPBE38	Beige	38	ARONA S1P SRC	3295249232696	13295249232693	10	1	10.5 kg	38.0 cm	56.6 cm	30.2 cm
ARONASPBE39	Beige	39	ARONA S1P SRC	3295249232702	13295249232709	10	1	11.1 kg	38.2 cm	56.8 cm	31.2 cm
ARONASPBE40	Beige	40	ARONA S1P SRC	3295249232719	13295249232716	10	1	11.6 kg	42.0 cm	62.0 cm	33.2 cm
ARONASPBE41	Beige	41	ARONA S1P SRC	3295249232726	13295249232723	10	1	12.4 kg	42.0 cm	61.4 cm	33.8 cm
ARONASPBE42	Beige	42	ARONA S1P SRC	3295249232733	13295249232730	10	1	12.2 kg	41.8 cm	61.8 cm	33.6 cm
ARONASPBE43	Beige	43	ARONA S1P SRC	3295249232740	13295249232747	10	1	12.4 kg	42.4 cm	61.2 cm	33.8 cm
ARONASPBE44	Beige	44	ARONA S1P SRC	3295249232757	13295249232754	10	1	13.3 kg	45.8 cm	66.0 cm	37.6 cm
ARONASPBE45	Beige	45	ARONA S1P SRC	3295249232764	13295249232761	10	1	14.1 kg	46.4 cm	66.4 cm	37.6 cm
ARONASPBE46	Beige	46	ARONA S1P SRC	3295249232771	13295249232778	10	1	14.0 kg	46.6 cm	65.6 cm	37.2 cm
ARONASPBE47	Beige	47	ARONA S1P SRC	3295249232788	13295249232785	10	1	14.1 kg	45.8 cm	66.8 cm	37.0 cm
ARONASPBE48	Beige	48	ARONA S1P SRC	3295249232795	13295249232792	10	1	14.6 kg	37.6 cm	66.4 cm	46.2 cm
ARONASPNO35	Black	35	ARONA S1P SRC	3295249232665	13295249232662	10	1	10.0 kg	37.8 cm	56.6 cm	30.4 cm
ARONASPNO36	Black	36	ARONA S1P SRC	3295249232832	13295249232839	10	1	10.3 kg	37.6 cm	56.8 cm	30.4 cm
ARONASPNO37	Black	37	ARONA S1P SRC	3295249232849	13295249232846	10	1	10.3 kg	37.8 cm	57.0 cm	30.4 cm
ARONASPNO38	Black	38	ARONA S1P SRC	3295249232856	13295249232853	10	1	11.0 kg	39.8 cm	56.8 cm	30.4 cm
ARONASPNO39	Black	39	ARONA S1P SRC	3295249232863	13295249232860	10	1	11.2 kg	39.6 cm	57.0 cm	30.0 cm
ARONASPNO40	Black	40	ARONA S1P SRC	3295249232870	13295249232877	10	1	12.0 kg	44.0 cm	61.4 cm	33.4 cm
ARONASPNO41	Black	41	ARONA S1P SRC	3295249232887	13295249232884	10	1	12.2 kg	43.2 cm	62.0 cm	33.6 cm
ARONASPNO42	Black	42	ARONA S1P SRC	3295249232894	13295249232891	10	1	12.8 kg	43.0 cm	61.8 cm	33.8 cm
ARONASPNO43	Black	43	ARONA S1P SRC	3295249232900	13295249232907	10	1	13.0 kg	43.0 cm	62.2 cm	33.8 cm
ARONASPNO44	Black	44	ARONA S1P SRC	3295249232917	13295249232914	10	1	13.7 kg	46.0 cm	66.8 cm	37.4 cm
ARONASPNO45	Black	45	ARONA S1P SRC	3295249232924	13295249232921	10	1	14.0 kg	46.0 cm	66.6 cm	36.8 cm



Safety footwear

ARONA S1P SRC

MANUFACTURING

Lightweight and flexible high cut shoe, for all-day comfort

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
ARONASPNO46	Black	46	ARONA S1P SRC	3295249232931	13295249232938	10	1	12.0 kg	64.5 cm	44.5 cm	35.5 cm
ARONASPNO47	Black	47	ARONA S1P SRC	3295249232948	13295249232945	10	1	15.0 kg	47.0 cm	66.4 cm	36.8 cm
ARONASPNO48	Black	48	ARONA S1P SRC	3295249232955	13295249232952	10	1	15.2 kg	46.4 cm	66.2 cm	37.6 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height