

PA1645

CRIMPER 1600 OPEN BARREL AWG 30-18

The PA1645's unique straight-sided die design enables users to crimp virtually any open barrel contact. This versatile crimper tool crimps pins, sockets, spring contacts, and open barrel slide-ons made by AMP, Molex, Burndy, Souriau, TRW, Cinch, ITT, Cannon, and Amphenol. Particularly useful when working with RS-232-type connectors.

CRIMPING RANGE

30-24 AWG (0.050-0.200 mm²)

22-18 AWG (0.340-0.750 mm²)

FEATURES:

- Straight-sided die design for virtually any open barrel contact
- Crimps pins, sockets, spring contacts, and open barrel slide-ons
- Works with Molex, Waldom & Leoco-type connectors
- Crimps non-insulated terminal lugs, cable lugs, parallel and serial splices, or F-Type
- Precision fixed dual-plate dies for crimp accuracy
- Durable steel construction
- Rubber-embedded ergonomic handles for low-effort operation
- Ratcheting mechanism with side-entry wire feed



Paladin® brand hand tools from Tempo® Communications carry a Limited Lifetime Warranty.

1390 Aspen Way Vista, CA • 92081 PA1645 04/26

Latin America Phone : 1.760.510.0558 | EMEA Phone: +44 (0) 1633 927050

©2026 Tempo Communications Inc. • An ISO 9001 Company

EMEA Office: Tempo Europe Limited

Brecon House • William Brown Close • Cwmbran • NP44 3AB • UK

TempoCom.com | tel 800.642.2155 | sales@tempocom.com



Renewed Vision. Innovation Forward.



Follow us on Social Media
@TempoComms