



Part Number : [936010690](#)
Product Description : GWconnect STD -
Standard, Single Lever Coupler, Polyamide,
with 1 Lever, Top Entry, Size 3A «21x21», M20
Thread, Grey White
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Number : 7803.6231.0



Documents & Resources

Drawings
[936010690_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Heavy-Duty Connectors
Series	93601
Description	GWconnect STD - Standard, Single Lever Coupler, Polyamide, with 1 Lever, Top Entry, Size 3A «21x21», M20 Thread, Grey White
Comments	IP67 with screw gasket.
Component Type	Single Lever Coupler
IP Rating	IP66
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191842776

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	230V / 400V
-------------------	-------------

Physical

Component Size	3A «21x21»
Entry Location	Top
Hood Color	Grey White RAL 9002
Lock to Mating Part	Yes
Material - Hood	Polyamide
Material - Lever	Polyamide
Net Weight	15.000/g
Number of Levers	1

Packaging Type	Bag
Thread Size	M20
Thread Type	(M) Metric

Use with Part(s)

Description	Part Number
Use With	Size 3A «21x21» S-A, S-D, and S-Q Inserts