

# KERN TVM5000N230N.

Premium-Prüfstand für professionelle Kraftmessungen

**KERN**<sup>®</sup>



## Functions

Electrical limit swiches:	yes
Repeat function:	yes
Speed display:	yes

## Environmental conditions

Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

## Power supply

Input voltage:	220 V AC 50 Hz
n/a:	EURO

## Category

Brand:	Sauter
Category:	Test stands
Product Group:	Electronic test stand

## Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	580 x 345 x 1200 mm
Gross weight:	83 kg
Net weight:	58 kg
Shipping method:	Freight forwarder

## Construction

Casing material:	Metal lacquered
Maximum generated force:	5 kN
Maximum travelling distance:	21 cm
Operation speed:	0,230 m/min
Operation speed:	0,010 m/min
Overall dimensions mounted (WxDxH):	400 x 256 x 1015 mm
Speed accuracy (of [Max]):	3 %
between the pillars:	21,500 cm