

LONG LIFE CUTTING MEDIUM THICK TOUGH METAL

EXPERT Medium-Thick Tough Metal Blades

EXPERT

- ① Exceptional durability is built in with Bosch Carbide Technology
- ② Wide body for precise, straight cuts
- ③ Fine teeth cut thinner material with ease



* vs. Bosch S1122BF



BOSCH

EXPERT MEDIUM-THICK TOUGH METAL S1155HHM BLADE



- ▶ Ideal for cutting tough metal pipes and profiles with medium wall thickness; capable of cutting stainless steel; and any hardened, high alloy or high strength steel
- ▶ Best for recycling and demolition workers: long lasting and powerful
- ▶ Lasts up to 50x longer than Bosch S1122BF blade in tough materials
- ▶ Fits all S-shank reciprocating saws



PRODUCT PROPERTIES							ORDERING INFORMATION				
Tooth spacing [mm]	Tooth pitch [TPI]	Dimensions LxWxT [mm]	Blade material abbreviation	Recommended min. material thickness [mm]	Recommended max. material thickness [mm]	Max. cut capacity [mm]	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number
2.5	10	225 x 25 x 1.1	CT	3	8	175	C1c	1	1	534 640	2 608 900 374
2.5	10	225 x 25 x 1.1	CT	3	8	175	C1c	3	1	534 657	2 608 900 375
2.5	10	225 x 25 x 1.1	CT	3	8	175	P1h	10	1	534 664	2 608 900 376



BOSCH