



## Datasheet

ENGLISH

# RS 13A, BS standard fixing, Passive, 2 Gang RCD Socket, Polycarbonate, Surface Mount, Switched, IP66, Outdoor, 250 V

RS Stock number: 699-7105



### Features

Stylish modern profile

Covers to seal the fixing screws

2 Earth terminals in socket

1 Earth terminal in mounting box

Cable entries in the 4 sides have removable blanking caps except for the middle entry on the bottom face which is prewired with a cable gland

Socket is prewired with 3m of 3 core 1.25mm<sup>2</sup> black flex to BS6500, the end of cable is prepared for wiring direct to the RCD plug

Cover will stay open to allow for easy access to sockets

See-through cover allows status of switches to be seen

RCD plug is non latching type

Suitable for temporary installation only

Latched type, 30mA trip current, 40mS trip

**Socket**

<b>Standard(s)</b>	BS 1363 Part 2
<b>Rating</b>	13 Amp 250V~
<b>Switch type</b>	Double pole
<b>Contact Gap</b>	3mm minimum
<b>Terminal Capacity</b>	3 x 2.5mm <sup>2</sup> 3 x 4mm <sup>2</sup> 2 x 6.0mm <sup>2</sup>
<b>IP rating</b>	IP56 with plug in use
<b>Covered by RoHS directive</b>	No
<b>Covered by WEEE directive</b>	No
<b>Size</b>	171mm x 154mm x 80mm
<b>Number of 20mm cable entries</b>	8 x 20mm. 1 in each of the 2 sides and 3 in each of the top and bottom faces 1 drill out entry 20/25mm in rear face

**RCD Plug**

<b>Standard(s)</b>	BS 7071
<b>Rating</b>	13 Amp 250V~
<b>Trip current</b>	30mA
<b>Covered by RoHS directive</b>	No
<b>Covered by WEEE directive</b>	No
<b>Size</b>	114mm x 51mm x 72mm